



SYSTEME DE STOCKAGE DE CMS



Opening an SMD Container

Boite E1 E4 Antistatique Ouverture automatique



CS.0002.0
Small SMD Container (right)

CS.0001.0
Large SMD Container (left)



922.110
Rail Unit with 12 small
SMD Containers (left)

922.310
Rail Unit with 3 large
SMD Containers (right)

Technical Details:

Storage Capacities:
CS 0002.0: approximately 250 Mini Meifs
CS 0001.0: approximately 1000 Mini Meifs
CS 0001.0 with IC Insert: 21 x SO16
or 8 x SO24



922.322
Insert SO 8- SO 16 (left)
for large SMD Containers.

922.323
Insert SO 16L- SO 28 (right)
for large SMD Containers.



922.113
Support with 36 small
SMD Containers
with 3 Rail Units 922.110.



922.313
Support with 9 large
SMD Containers
with 3 Rail Units 922.310.



942.008
IC Apportioner IP 942
For easy charging of Inserts with ICs
from sticks. Each operation lets just
the correct number of ICs slide into the
Insert.



922.207
Antistatic Drawer Unit.
With 6 drawers, 1 drawer filled with 7
Rail Units 922.110, providing 84 small
SMD Containers.



922.242
Antistatic Drawer Unit.
With 6 drawers, each filled with 7 Rail
Units 922.110, providing 504 small
SMD Containers.



922.314
Antistatic Drawer Unit.
With 6 drawers, 1 filled with 7 Rail
Units 922.110 and 1 filled with
7 Rail Units 922.310, providing 84
small SMD Containers and 21 large
ones.